



**12120**

LOW PROFILE SIDE CLAMPING

**Material**

Ribbed face steel, hardened and plated.  
Screw steel hardened, strength class 10,9.

**Technical Notes**

For clamping workpieces with uneven

surfaces, this clamp provides serrations to help the clamp grip the workpiece.

**Tips**

Clockwise rotation is recommended. The workpiece should be to the right of the

clamp. For replacement cam screws see parts 12112.

**Important Notes**

$w_1$  is distance to drill and tap from edge of workpiece.

Order No.	$d_1$	$d_2$	$h_1$	$l_1$	Clamping force kN	Stroke $s_1$	$w_1$	A/F	Torque to Nm max.	Qty/pack	Weight g
12120.W0020	M10x1,5	20.60	6.35	19.0	8.8	1.22	10.2	7	28	8	40
12120.W0025	M12x1,75	25.40	9.52	22.8	17.7	2.03	12.7	8	88	8	45
12120.W0030	M16x2	30.15	12.70	28.5	26.6	2.54	15.0	12	135	4	90

