



Coolant Nozzles - Manifold





20114

Material

Manifold: anodized aluminium. Thread connectors: brass.

Pipe plugs: plated steel.

Thread union: brass.

Technical Notes

Max. temperature: 70°C.

Max. pressure: 33 bar.

Order No. 20114.W2250

 d_1 1/4" NPT

 d_2 1/4" NPT/BSPT

 h_1 76.2

 h_2 25.4

 I_1 88.9

 I_2 31.8

A/F 1-3/16" COOLANT NOZZLES




Clamping Torque




11040/CL2040						
Clamping Torque	Clamping Force					
N/m	N					
50	23000					
40	18000					
30	12500					
25	11500					
20	9500					



11070/CL2070						
Clamping Torque	Clamping Force					
N/m	N					
60	16500					
50	15000					
40	12000					
30	10000					
25	8000					
20	7000					







10940/CL0030						
Clamping Torque	Clamping Force					
N/m	N					
8.5	4000					
8	3800					
7	3400					
6	3000					
5	2500					
4	2000					





System pressure (bar)	0.35	0.7	1.4	2.0	2.8	4.1	5.5		
Orifice diameter (mm)	Flow rate (litres/minute)								
1.02	0.32	0.45	0.64	0.77	0.91	1.18	1.41		
1.57	0.86	1.14	1.68	2	2.32	2.82	3.32		
2.18	1.64	2.32	3.27	3.86	4.55	5.46	6.82		
2.79	2.91	4.09	6.36	7.27	8.18	10	11.37		
4.06	6.36	9.09	12.73	15.91	18.18	21.82	25.46		
5.59	11.37	16.82	23.64	30.46	35.46	42.28	48.19		
System pressure (bar)	6.9	10.3	13.8	20.7	34.5	69.0	103.5		
Orifice diameter (mm)	Flow rate (litres/minute)								
1.02	1.59	1.86	2.09	2.77	4	5.46	6.36		
1.57	3.64	4.55	5.46	6.82	9.55	13.64	17.28		
2.18	7.73	9.09	10.46	12.73	16.82	23.64	28.64		
2.79	14.09	16.37	18.64	23.64	29.55	40.46	49.55		
4.06	28.19	34.55	41.37	49.1	63.65	90.01	110.47		
5.59	53.64	65.46	75.01	89.1	114.56	161.39	197.75		

What Flow Rate of Coolant is Required?

Choose a nozzle with an orifice size that matches your pump's capacity.

Select an orifice size too big and coolant pressure will drop off, an orifice size too small and an inadequate amount of coolant will reach the tool tip and can result in damage.

Note: Flow rates are based on water at 20°. Actual results may vary with fluid type, extension length and aiming angle.

To calculate the average coolant exit velocity (important in some grinding operations where it is often desirable to match or exceed the peripheral velocity of the wheel) refer to the formula below. Choose an orifice size that produces sufficient back pressure to achieve the desired velocity.

Calculating Coolant Velocity

 $V = \frac{(17.11 \times 10^{-5}) \times F}{(d \times 10^{-3})^2}$

Where;

V = Velocity in m/s

 $C = Constant of 17.11 x 10^{-5}$

F = Flow rate through orifice in litres/min (see table above)

d = Orifice diameter (mm) from product tables

Choose a nozzle extension that suits your application. Short projections are more compact and less likely to be knocked out of position by swarf or vibration. Longer extensions are easier to aim, produce a more streamline or laminar flow and shoot further.

Nozzle Extensions

The most common coolant pump on CNC machine tools is a single stage centrifugal pump, normally designed to move high volumes of water at low pressure (typically 0.2 to 1.4 bar). Multi-stage centrifugal pumps are capable of higher pressures (typically 1.4 to 14 bar) while still producing high flow rates. Positive displacement pumps are used for very high pressure applications up to 140 bar and are generally used with small diameter orifices due to their lower flow rates.

A Word About Coolant Pumps





ov-W20000-A-T-W20114-A-T-b-rnh - Updated - 26-10-2022