



33944

Material

Body and Shank: stainless steel SUS303 Pin, Knob, Spring: stainless steel SUS304.

Technical Notes

One-touch fasteners are the ideal solution for applications requiring rapid and recurring change over of tooling or set ups. Use in applications as diverse as bottling processes, machine covers, changing of cogs and drive belts. One-touch fasteners provide a quick, simple and secure change over solution - no time wasted in unfastening screws or other permanent fixings, and no opportunity for lost fixings in your machinery.

Temperature resistant to 200°C.

Important Notes


Suitable for panels/enclosures of 6 to 20

mm thickness. For locating bushes see part no. 33948 and 33949.

Actuation:

- -Turn handle to off position: present cover panel to frame and align to locating bush.
- -Turn handle 45° to on position: locking pin follows cam, tightening fastener and securely fastening panel.

Order No.	For single panel thickness	Clamping force N	d ₁ -0.04 - 0.08	d ₂ tol. h9	d ₃	d ₄	d ₅	l ₁	h ₁	h ₂	m	Shear strength N	Tensile strength N	Weight g
33944.W1005	6-10	60	5	14	25	25	21	15,5	11,5	6,5	M 2x0,4	1800	1200	35
33944.W1408	6-14	90	8	18	34	34	28	17,0	14,0	10,0	M 3x0,5	3200	2600	80
33944.W2008	12-20	90	8	18	34	34	28	23,0	14,0	10,0	M 3x0,5	3200	2600	85







ov-W33910-A-T-W33956-A-T-one-touch-fasteners-a-lnh - Updated - 27-10-2022

One-Touch Fasteners - Alternatives to Screws









Easy & Secure! For Quick Changeover with No Tools!























One-Touch Fasteners

quick-easy-secure




One-Touch Change Over







Installation and Removal of Rotary Blades and **Changes of Shooters**



Changes of Star Wheels and Guide Plates





Changes of Pusher and Changes of Chuck **Handling Machines**



ov-W33910-A-T-W33956-A-T-one-touch-fasteners-b-rnh - Updated - 27-10-2022