


Acetal Body Ball Transfer Units light duty, acetal body





67204

Material

Acetal (POM) housing with acetal or stainless (AISI 316) balls.

Technical Notes

Push-fit units, these actetal units resist

salt water and chemicals.
They are non-conductive and non-magnetic, low friction 1:0,03.
Temperature range -20°C to +70°C, speeds up to 1m/s.

Tips

These rollers can only be used in the horizontal or "ball up" direction.

Order No.	d_1	d_2	h_1	h ₂	d_3	h ₃	Housing	Ball
67204.W0156	15	31	21	9.5	24	11.5	Acetal	Stainless
67204.W0157	15	31	21	9.5	24	11.5	Acetal	Acetal
67204.W0226	22	45	30.5	9.8	36	20.7	Acetal	Stainless
67204.W0227	22	45	30.5	9.8	36	20.7	Acetal	Acetal
67204.W0306	30	55	37	13.8	45	23.2	Acetal	Stainless
67204.W0307	30	55	37	13.8	45	23.2	Acetal	Acetal
67204.W0456	45	75	53.5	19	62	34.5	Acetal	Stainless
67204.W0457	45	75	53.5	19	62	34.5	Acetal	Acetal



TRANSFER ROLLERS

Materials Handling

Wixroyd Ball Transfer Units selection



Product selection

Available materials

Housing	Ball	Load Factor	
Steel	Steel	1,0	Housing: AISI 1040 steel, machined, toughened & zinc plated. Ball: AISI 52100 chrome steel
Steel	Stainless	0,7	Housing: AISI 1040 steel, machined, toughened & zinc plated. Ball: AISI 420 stainless steel
Stainless	Stainless	0,7	Housing: AISI 416 stainless steel. Ball: AISI 420 stainless steel
Steel	Acetal		Housing: AISI 1040 steel, machined, toughened & zinc plated. Ball: POM acetal
Aluminium Stainless		;	Housing: aluminium. Ball: AISI 420 stainless steel
Acetal	Acetal		Housing: POM acetal. Ball: POM acetal
Acetal	Stainless	i	Housing: POM acetal. Ball: AISI 420 stainless steel

Fixing clip selection

P	art No.	Ball Size	Minimum Bore ø	Maximum Bore ø
672	02.W9015	15	24,8	25,0
672	02.W9022	22	37,0	37,2
672	02.W9030	30	46,3	46,7

Clip requires a minimum plate thickness of 3mm to grip securely

How to select the correct unit

Ball Type	Max Load (Kg)	Friction (% of load)	Speed (m/s)	Shock Loads	Arduous Conditions	Orientation	Instant Change
Medium Duty	20-3500	2%	1,5	111	11		111
Light Duty	7-250	3%	1,0	✓	//		111

Variables to consider



Shock Loads: Specify High Capacity series & spring loaded units



Track Hardness/ Conveyed Item Material: Standard material ball units have Rockwell 'C' hardness of 60 minimum




Delicate Surfaces: Ball Units - Acetal (POM) & Phenolic Resin



Operating Environment: Wet, dirty, outdoor, radioactive

Operation temperature




% Load Capacity




Wixroyd Ball Transfer Unit





Load and stability

To determine the load of a ball transfer unit, the weight of the article to be conveyed should be divided by 3. If the height tolerance of the load balls is good and the surface of the workpiece to be conveyed is suitable, the calculation can be based on the number of ball transfer units under the load.



Pitching and spacing

How the ball transfer units should be arranged depends on the bottom surface of the load to be transported. For loads with a uniform, even bottom surface, e.g. packing cases, the distance between the ball transfer units is calculated by dividing the smallest dimension by 3,5.

The maximum conveying speed allowed amounts to 2m/s. The load capacities specified apply to any mounting position and are based on 10⁶ rotations of the load ball. With the units being used over a longer time at speeds exceeding 1m/s, an increase in temperature as well as a reduction in travel life must be expected depending on the load.

Conveying speed and load capacity

$$L = \frac{C^3}{F} \cdot 10^6 \text{ rotations}$$


L = travel life C = load capacity (N)

F = load(N)

Calculation of travel life

The diagram shows the friction values as a function of load and speed for ball transfer units. These approximate values apply to all mounting positions with operation on a hardened steel plate.

v = 1m/s



Friction



ov-W67200-AP2705-T-W67224-A-T-b-rnh- Updated -31-10-2022