


## Heavy Duty Hook Toggle Clamp for high retaining force

## Heavy Duty Toggle Clamps





46030

## Material

Foot, lever, arm and catch: cast steel, black oxide coated.

Strap, pins and nuts: steel, heat treated and zinc plated.

Pins: hardened, ground and permanently lubricated.

Handle: ergonomic soft feel, oil-resistant, with large grip area.

Supplied complete with counter catch.

## **Technical Notes**

Four mounting holes in both foot and

catch.

Circlips are used to retain pins in bearing bushes, and to centre the clamping pin. Temperature range -10°C to +80°C.

Order No.	Size	F <sub>1</sub> kN	Adj. distance	Stroke s <sub>1</sub>	$h_1$	h <sub>2</sub>	$I_1$	l <sub>2</sub>	Weight g
46030.W0204	4	15	66	44	228	122	245-311	183	2830
46030.W0205	5	27	65	47	285	146	313-378	238	4020
Order No.	l <sub>3</sub>	I <sub>4</sub>	I <sub>5</sub>	l <sub>6</sub>	l <sub>7</sub>	$w_1$	$W_2$	$d_1$	$d_2$
46030.W0204	42-107	24-90	68	45	28	64	45	10	8.5
46030.W0205	49-114	28-93	86	57	35	82	57	12	10.5

